

**1499925-6****SL110 Series Modular Jack, RJ45, category 6, HD, unshielded, without dust cover, blue**

## Product Classification

Portfolio	NETCONNECT®
Product Series	SL Series
Product Type	Modular jack
Regional Availability	Asia   Latin America   North America

## Body Features

110 Block Material	Polycarbonate
Inverted Jack Face	Yes

## Configuration Features

Keyed	No
Number of Positions	8
Wiring Pattern	Universal

## Contact Features

Contact Base Material	Beryllium copper
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Thickness	50.00 µin   1.27 µm

## Dimensions

Insulated Conductor Outside Diameter	0.057 in   1.45 mm
Solid Wire Range	.51 mm <sup>2</sup>   .65 mm <sup>2</sup>
Stranded Wire Range	.14 mm <sup>2</sup>   .2 mm <sup>2</sup>
Wire Range	22 AWG   24 AWG   26 AWG

## Housing Features

Housing Color	Blue
Housing Material	Polycarbonate

## Industry Standards

Standards Compliance	UL 94 V-0
----------------------	-----------

## Mechanical Attachment

1499925-6

Mounting Type	SL Series Faceplate
---------------	---------------------

## Packaging Features

Packaging Method	Poly Bag
Packaging Quantity	1

## Product Type Features

Performance Category	Category 6
Shielded	No
Applies To	Panel
Cable Type	Unshielded Twisted Pair
Connector Type	Connector Assembly
Dust Cover	Without
Jack Type	RJ45

## Termination Features

Termination Method to Wire/Cable	Insulation Displacement Crimp (IDC)
Termination Style	SL Termination Tool

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant