

**1711091-5****RJ45 Patch Cord, category 6, UTP, stranded, 5 m, white****This product will be discontinued on: May 1, 2018****Replaced By**

NPC06UZDB-WT005M NPC RJ45 Patch Cord, category 6, U/UTP, LSZH, 5 m, white

Product Classification

Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord
Regional Availability	Asia Australia/New Zealand EMEA

Dimensions

Cord Length	5 m
Diameter Over Jacket	6 mm

Electrical Specifications

ANSI/TIA Category	6
-------------------	---

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)

General Specifications

Cable Type	U/UTP (unshielded)
Interface, connector A	RJ45 plug
Interface, connector B	RJ45 plug
Jacket Color	White
Pairs, quantity	4

Mechanical Specifications

Conductor Type	Stranded
Conductor Gauge, stranded	26 AWG

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU**Classification**
Compliant