



1711160-2

**AMP-TWIST SL-Series Modular Jack, category 6A, shielded, 4 pair, for FTP cables, rear exit, with dust cover**

## Product Classification

Portfolio	NETCONNECT®
Product Series	SL Series
Product Type	Modular jack
Regional Availability	Australia/New Zealand   EMEA   Latin America

## Body Features

Color	Silver gray
110 Block Material	Polycarbonate
Cover Color	Transparent
Cover Material	Polycarbonate
Shield Material	Stainless steel

## Configuration Features

Keyed	No
Number of Positions	8
Wiring Pattern	Universal

## Contact Features

Contact Base Material	Beryllium copper
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Thickness	50.00 µin   1.27 µm

## Dimensions

Cable Diameter, maximum	9.00 mm   0.35 in
Insulated Conductor Outside Diameter	0.0629 in   1.6 mm
Panel Thickness, recommended	1.60 mm   0.06 in
Solid Wire Range	24 – 22 AWG
Stranded Wire Range	26 – 24 AWG

## Housing Features

Housing Color	Gray
Housing Material	Zamak 5

## Packaging Features

1711160-2

Packaging Method	Box   Tray/Box
Packaging Quantity	12

## Product Type Features

Performance Category	Category 6A
Shielded	Yes
Applies To	Panel
Connector Type	Connector Assembly
Dust Cover	With
Jack Type	RJ45

## Termination Features

Termination Method to Wire/Cable	Insulation Displacement Crimp (IDC)
Termination Style	SL Termination Tool

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant