



1711592-1

AMP-TWIST SL-Series Modular Jack, category 6A, shielded, 8-position, with dust cover

Product Classification

Portfolio	NETCONNECT®
Product Series	SL Series
Product Type	Modular jack
Regional Availability	Australia/New Zealand EMEA Latin America

Body Features

Color	Silver gray
110 Block Material	Polycarbonate
Cover Color	Black
Cover Material	Polycarbonate

Configuration Features

Keyed	No
Number of Positions	8
Wiring Pattern	Universal

Contact Features

Contact Base Material	Beryllium copper
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Thickness	50.00 µin 1.27 µm

Dimensions

Cable Diameter, maximum	9.00 mm 0.35 in
Height	21.50 mm 0.85 in
Insulated Conductor Outside Diameter	0.0629 in 1.6 mm
Panel Thickness, recommended	1.60 mm 0.06 in
Solid Wire Range	24 – 22 AWG
Stranded Wire Range	26 – 24 AWG

Housing Features

Housing Color	Gray
Housing Material	Zamak 5

1711592-1

Packaging Features

Packaging Method	Box Tray/Box
Packaging Quantity	12

Product Type Features

Performance Category	Category 6A
Shielded	Yes
Applies To	Panel
Connector Type	Connector Assembly
Dust Cover	With
Jack Type	RJ45

Termination Features

Termination Method to Wire/Cable	Insulation Displacement Crimp (IDC)
Termination Style	SL Termination Tool

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant