

**1711817-5****RJ45 Patch Cord, category 6A, S/FTP, LSZH, stranded, gray, 5 m**

**This product will be discontinued on: May 1, 2018**

**Replaced By**

NPC6ASZDB-GY005M    NPC RJ45 Patch Cord, category 6A, S/FTP, LSZH, 5 m, gray

## Product Classification

Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord
Regional Availability	Asia   Australia/New Zealand   EMEA

## Dimensions

Cord Length	5 m
Diameter Over Jacket	6 mm

## Electrical Specifications

ANSI/TIA Category	6A
-------------------	----

## Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)

## General Specifications

Cable Type	S/FTP (shielded)
Interface, connector A	RJ45 plug
Interface, connector B	RJ45 plug
Jacket Color	Gray
Pairs, quantity	4

## Mechanical Specifications

Conductor Type	Stranded
Conductor Gauge, stranded	26 AWG

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU**Classification**  
Compliant