

**294658****Cushion Hanger Assembly for 7/8 in corrugated coaxial cable, four holes**

## Dimensions

Nominal Size	7/8 in
Compatible Diameter, maximum	30.988 mm   1.220 in
Compatible Diameter, minimum	26.670 mm   1.050 in
Height	25.40 mm   1.00 in
Length	96.00 mm   3.78 in
Width	79.75 mm   3.14 in

## Electrical Specifications

DTF Effect	0.1 dB
Return Loss Effect	0.1 dB

## General Specifications

Hanger Type	Cushion hanger
Brand	I-Line
Cables per Hanger	4
Color	Black
Material Type	Engineered plastic
Ordering Note	CommScope® non-standard product
Package Quantity	10

## Mechanical Specifications

Corrosion Resistance, minimum with no degradation	=500 hours in salt spray chamber
Mounting	3/8 in (M10) drilled cable ladder
Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
UV Resistance, minimum with no degradation	=100 hours exposure in accelerated UV life chamber
Vibration Survival	=4 hours at resonant frequency
Environmental Strength Capability	Double cable weight

## Packed Dimensions

Height	17.0 cm   6.7 in
Length	10.0 cm   3.9 in
Shipping Weight	0.44 kg   0.96 lb
Width	13.0 cm   5.1 in