

**2111475-6****E Series Keystone Modular Jack, 8-position, category 6, unshielded UTP, RJ45, blue**

## Product Classification

Portfolio	NETCONNECT®
Product Series	E Series
Product Type	Modular jack
Regional Availability	Asia   Latin America   North America

## Body Features

110 Block Material	Polycarbonate
--------------------	---------------

## Configuration Features

Keyed	No
Number of Positions	8
Wiring Pattern	T568A/T568B

## Contact Features

Contact Base Material	Beryllium copper
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Thickness	50.00 µin   1.27 µm

## Dimensions

Cable Diameter, maximum	5.80 mm   0.23 in
Insulated Conductor Outside Diameter	0.057 in   1.45 mm
Solid Wire Range	.51 mm <sup>2</sup>   .65 mm <sup>2</sup>   22 AWG   24 AWG
Stranded Wire Range	.14 mm <sup>2</sup>   .2 mm <sup>2</sup>   24 AWG   26 AWG

## Housing Features

Housing Color	Blue
Housing Material	Polycarbonate

## Industry Standards

Standards Compliance	UL 94 V-0
----------------------	-----------

## Mechanical Attachment

Mounting Type	KL Series Faceplate   Panel Mount
---------------	-----------------------------------

2111475-6

## Packaging Features

Packaging Method	Poly Bag
------------------	----------

## Product Type Features

Performance Category	Category 6
Shielded	No
Connector Style	Keystone
Connector Type	Connector Assembly
Dust Cover	Without
Jack Type	RJ45

## Termination Features

Termination Method to Wire/Cable	Insulation Displacement Crimp (IDC)
Termination Style	SL Termination Tool

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant