

**219413-3****Copper Cable, category 5e, 4 pair, FTP, PVC, 24 AWG solid, 1000 m reel, white**

## Product Classification

Portfolio	NETCONNECT®
Product Type	Twisted pair cable
Regional Availability	EMEA

## Standards And Qualifications

EN50575 CPR Cable EuroClass Eca

## Construction Materials

Jacket Material	PVC
Conductor Material	Bare copper
Insulation Material	Polyolefin
Shield (Tape) Material	Aluminum/Polyester

## Dimensions

Cable Length	1000 m   3281 ft
Diameter Over Jacket	6.100 mm   0.240 in

## Electrical Specifications

ANSI/TIA Category	5e
Transmission Standards	ANSI/TIA-568-C.2   CENELEC EN 50288-6-1   ISO/IEC 11801 Class E

## Environmental Specifications

Operating Temperature	-40 °C to +75 °C (-40 °F to +167 °F)
-----------------------	--------------------------------------

## General Specifications

Cable Type	F/UTP (shielded)
Packaging Type	Reel
Pairs, quantity	4
Cable Component Type	Horizontal
Jacket Color	White
Brand	NETCONNECT®
Conductor Gauge, singles	24 AWG
Conductor Type, singles	Solid
Conductors, quantity	8

## Regulatory Compliance/Certifications

# Product Specifications



219413-3

---

**Agency**

RoHS 2011/65/EU  
CENELEC

---

**Classification**

Compliant