

**219420-2****Copper Cable, category 5e, 4 pair, FTP, LSZH, 24 AWG solid, 305 m pull-box, white**

Product Classification

| | |
|-----------------------|--------------------|
| Portfolio | NETCONNECT® |
| Product Type | Twisted pair cable |
| Regional Availability | EMEA |

Standards And Qualifications

EN50575 CPR Cable EuroClass Dca | s2 | d2 | a1

Construction Materials

| | |
|------------------------|-------------------------------|
| Jacket Material | Low Smoke Zero Halogen (LSZH) |
| Conductor Material | Bare copper |
| Insulation Material | Polyolefin |
| Shield (Tape) Material | Aluminum/Polyester |

Dimensions

| | |
|----------------------|---------------------|
| Cable Length | 305 m 1000 ft |
| Diameter Over Jacket | 6.200 mm 0.244 in |

Electrical Specifications

| | |
|------------------------|---|
| ANSI/TIA Category | 5e |
| Transmission Standards | ANSI/TIA-568-C.2 CENELEC EN 50288-6-1 ISO/IEC 11801 Class E |
| Safety Voltage Rating | 40 V |

General Specifications

| | |
|--------------------------|------------------|
| Cable Type | F/UTP (shielded) |
| Packaging Type | Pull box |
| Pairs, quantity | 4 |
| Cable Component Type | Horizontal |
| Jacket Color | White |
| Brand | NETCONNECT® |
| Conductor Gauge, singles | 24 AWG |
| Conductor Type, singles | Solid |
| Conductors, quantity | 8 |

Regulatory Compliance/Certifications

| Agency | Classification |
|-----------------|----------------|
| RoHS 2011/65/EU | Compliant |

219420-2

CENELEC

EN 50575 compliant, Declaration of Performance (DoP) available