

2-599146-5

**Fiber Optic Cable, 8-fiber, OM1, orange**

## Product Classification

Portfolio	NETCONNECT®
Product Type	Fiber indoor/outdoor cable
Regional Availability	Asia   Australia/New Zealand   EMEA

## Standards And Qualifications

EN50575 CPR Cable EuroClass Dca | s2 | d1 | a1

## Construction Materials

Jacket Color	Orange
Total Fiber Count	8

## Body Features

Bend Radius (Installation)	90.00 mm   3.54 in
Bend Radius (Long Term)	60.00 mm   2.36 in
Tensile Strength (Installation)	1000.00 N   224.81 lbf
Tensile Strength (Long Term)	600.00 N   134.89 lbf
Weight (Nominal)	35.0 kg/km

## Dimensions

Length	2000.00 m   6561.68 ft
Outside Diameter	6.00 mm   0.24 in

## Industry Standards

Flammability Rating	ULSZH (Universal Low Smoke Zero Halogen)
---------------------	--

## Operation/Application

Environment	Outdoor
-------------	---------

## Product Type Features

Armoring	None
Cable Type	Fiber Optic
Fiber Cable Buffering	Tight buffer
Fiber Diameter	62.5/125 µm
Fiber Specification	IEC 60794-1
Fiber Type	OM1
Optical Mode	Multimode

## Signal Characteristics

Attenuation, maximum (1300nm) 1.50 dB/km

2-599146-5

## Usage Conditions

---

Installation Temperature Range -5 – 50 °C  
Operating Temperature Range -20 – 70 °C  
Storage Temperature Range -20 – 70 °C

## Regulatory Compliance/Certifications

---

### Agency

RoHS 2011/65/EU

### Classification

Compliant