

**406248-1****AMPINNERGY® Duplex Receptacle, shared neutral, standard ground, 5/8-wire (3-1-1/4-2-2), Line 1**

- Mates with power junction boxes and modular power strips
- Designed to accommodate field “plug-and-play” changes for phase and load balancing
- Fully polarized and keyed with clearly indicated active line

Product Classification

Brand	AMPINNERGY®
Product Series	AMPINNERGY
Product Type	Receptacle, ac
Regional Availability	North America

Body Features

Color	Black
-------	-------

Configuration Features

Line Type	Line 1 with standard ground
Neutral Type	Shared
Port Style	Duplex
Wiring Pattern	5-Wire/3 Circuit (3-1-1) 8-Wire/4 Circuit (4-2-2)

Dimensions

Panel Thickness, recommended	50.80 mm 2.00 in
------------------------------	--------------------

Electrical Characteristics

Current Rating	20 A
Voltage Rating	125 Vac

Industry Standards

Standards Compliance	NEMA 5-20R
----------------------	------------

Packaging Features

Packaging Method	Bag/Carton
Packaging Quantity	1

Regulatory Compliance/Certifications

Agency RoHS 2011/65/EU	Classification Compliant
----------------------------------	------------------------------------