

5-554169-3

**RJ45 Plug, category 5e, 8-position, unshielded, round cable, stranded wire**

## **OBSOLETE**

### **Replaced By**

6-557315-3  
MP-88U-R-1

Modular Plug Kit, 8P/8C, unshielded, round, 5.1 mm max cable jack OD, 8-position, 100/bag

## Product Classification

Portfolio	NETCONNECT®
Product Type	Modular plug
Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Body Features

Conductor Type	Stranded
----------------	----------

## Configuration Features

Number of Positions	8
Keyed	No

## Contact Features

Contact Base Material	Phosphor bronze
Number of Contacts Loaded	8

## Dimensions

Cable Jacket Outside Diameter Range	0.21 in   5.33 mm
Conductor Wire Size	28–26 AWG
Insulated Conductor Outside Diameter	0.029–0.039 in   0.74–0.99 mm

## Housing Features

Housing Material	Glass filled polycarbonate
------------------	----------------------------

## Industry Standards

Standards Compliance	UL 94 V-2
----------------------	-----------

## Packaging Features

Packaging Quantity	100
--------------------	-----

## Product Type Features

Performance Category	Category 5
Cable Style	Round
Connector Style	Plug

# Product Specifications



5-554169-3

Latch Style  
Shielded

Standard  
No