

5-554710-2

Modular Plug Assembly, RJ11, category 3, 26–28 AWG, 6-position

OBSOLETE

Replaced By

6-554710-2
MP-66U-R-5

Modular Plug, 6P/6C, unshielded, standard body, round, 4.6 mm cable jack OD, 6-position, category 3, 500/bag

Product Classification

Portfolio	NETCONNECT®
Product Type	Modular plug
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Body Features

Conductor Type	Stranded
----------------	----------

Configuration Features

Number of Positions	6
Keyed	No

Contact Features

Contact Base Material	Phosphor bronze
Number of Contacts Loaded	6

Dimensions

Cable Jacket Outside Diameter Range	0.18 in 4.58 mm
Conductor Wire Size	28–26 AWG
Insulated Conductor Outside Diameter	0.029–0.039 in 0.74–0.99 mm

Housing Features

Housing Material	Glass filled polycarbonate
------------------	----------------------------

Industry Standards

Standards Compliance	UL 94 V-2
----------------------	-----------

Packaging Features

Packaging Quantity	1000
--------------------	------

Product Type Features

Performance Category	Category 3
Cable Style	Round
Connector Style	Plug

Product Specifications

5-554710-2

Latch Style	Standard
Shielded	No