

5-554720-2

RJ45 Modular Plug Assembly, category 5e, unshielded, 8-position, 24–26 AWG, solid wire

OBSOLETE

This product was discontinued on: April 1, 2016

Replaced By

6-554720-2
MP-88U-F-5

Modular Plug Kit, 8P/8C, unshielded, flat oval, 2.54 x 8.89 mm max cable jack OD, 8-position, 500/bag

Product Classification

Portfolio	NETCONNECT®
Product Type	Modular plug
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Body Features

Conductor Type	Solid
----------------	-------

Configuration Features

Number of Positions	8
Keyed	No

Contact Features

Contact Base Material	Phosphor bronze
Number of Contacts Loaded	8

Dimensions

Cable Jacket Outside Diameter Range	0.1–0.35 in 2.54–8.89 mm
Conductor Wire Size	26–24 AWG
Insulated Conductor Outside Diameter	0.035–0.039 in 0.89–0.99 mm

Housing Features

Housing Material	Glass filled polycarbonate
------------------	----------------------------

Industry Standards

Standards Compliance	UL 94 V-2
----------------------	-----------

Packaging Features

Packaging Quantity	500
--------------------	-----

Product Type Features

Performance Category	Category 5
Cable Style	Flat Oval

Product Specifications



5-554720-2

Connector Style	Plug
Latch Style	Standard
Shielded	No