

5-569552-3

**RJ45 Plug, category 5e, 8-position, shielded**

## **OBSOLETE**

### **Replaced By**

6-569550-3  
MP-5ES-1

Modular Plug Kit, category 5e, 8P/8C, shielded, 4.8 – 5.6 mm max cable jack OD, 8-position,  
100/bag

## **Product Classification**

Portfolio	NETCONNECT®
Product Type	Modular plug
Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America

## **Body Features**

Conductor Type	Stranded
Shield Material	Copper alloy

## **Configuration Features**

Number of Positions	8
Keyed	No

## **Contact Features**

Contact Base Material	Phosphor bronze
Number of Contacts Loaded	8

## **Dimensions**

Cable Jacket Outside Diameter Range	0.19–0.199 in   4.83–5.08 mm
Conductor Wire Size	26–24 AWG
Insulated Conductor Outside Diameter	0.035–0.039 in   0.89–0.99 mm

## **Housing Features**

Housing Material	Glass filled polycarbonate
------------------	----------------------------

## **Industry Standards**

Standards Compliance	UL 94 V-2
----------------------	-----------

## **Packaging Features**

Packaging Quantity	100
--------------------	-----

## **Product Type Features**

Performance Category	Category 5e
Cable Style	Round

# Product Specifications



5-569552-3

Connector Style	Plug
Latch Style	Standard
Shielded	Yes