

**57538-2****Copper Cable, category 5e, 4 pair, UTP, LSZH, 24 AWG solid, 305 m pull-box, white**

Product Classification

Portfolio	NETCONNECT®
Product Type	Twisted pair cable
Regional Availability	EMEA

Standards And Qualifications

EN50575 CPR Cable EuroClass Eca

Construction Materials

Jacket Material	Low Smoke Zero Halogen (LSZH)
Conductor Material	Bare copper
Insulation Material	Polyolefin

Dimensions

Cable Length	305 m 1000 ft
Diameter Over Jacket	5.000 mm 0.197 in

Electrical Specifications

ANSI/TIA Category	5e
Transmission Standards	ANSI/TIA-568-C.2 CENELEC EN 50288-6-1 ISO/IEC 11801 Class D

Environmental Specifications

Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
-----------------------	-------------------------------------

General Specifications

Cable Type	U/UTP (unshielded)
Packaging Type	Pull box
Pairs, quantity	4
Cable Component Type	Horizontal
Jacket Color	White
Brand	NETCONNECT®
Conductor Gauge, singles	24 AWG
Conductor Type, singles	Solid
Conductors, quantity	8

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

57538-2

RoHS 2011/65/EU
CENELEC

Compliant
EN 50575 compliant, Declaration of Performance (DoP) available