Product Specifications





6-219590-4 | TE510M-GYMI-AP

510 Series Copper Cable, category 5e, 4 pair, U/UTP, 24 AWG, 305m, gray

Product Classification

Portfolio NETCONNECT®
Product Series 510 Series

Product Type Twisted pair cable

Regional Availability Asia

Construction Materials

Jacket Material PVC

Conductor Material Bare copper Insulation Material Polyolefin

Dimensions

Cable Length 305 m | 1000 ft
Diameter Over Jacket 4.900 mm | 0.193 in

Electrical Specifications

ANSI/TIA Category 5e

Transmission Standards ANSI/TIA-568-C.2 | CENELEC EN 50288-6-1 | ISO/IEC 11801 Class D

Environmental Specifications

Operating Temperature -20 °C to +60 °C (-4 °F to +140 °F)

General Specifications

Cable Type U/UTP (unshielded)

Packaging Type Reelex Pairs, quantity 4

Cable Component Type Horizontal
Jacket Color Gray
Product Number 510M

Brand NETCONNECT®

Conductor Gauge, singles 24 AWG
Conductor Type, singles Solid
Conductors, quantity 8

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant