



6-219590-8 | TE510M-YLMI-AP

510 Series Copper Cable, category 5e, 4 pair, UTP, CM rated, 24 AWG, 1000 ft, yellow

Product Classification

Portfolio	NETCONNECT®
Product Series	510 Series
Product Type	Twisted pair cable
Regional Availability	Asia

Construction Materials

Jacket Material	PVC
Conductor Material	Bare copper
Insulation Material	Polyolefin

Dimensions

Cable Length	305 m 1000 ft
Diameter Over Jacket	4.900 mm 0.193 in

Electrical Specifications

ANSI/TIA Category	5e
Transmission Standards	ANSI/TIA-568-C.2 CENELEC EN 50288-6-1 ISO/IEC 11801 Class D

Environmental Specifications

Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
-----------------------	-------------------------------------

General Specifications

Cable Type	U/UTP (unshielded)
Packaging Type	Reel
Pairs, quantity	4
Cable Component Type	Horizontal
Jacket Color	Yellow
Product Number	510M
Brand	NETCONNECT®
Conductor Gauge, singles	24 AWG
Conductor Type, singles	Solid
Conductors, quantity	8

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant