

**6536501-3****Fiber Optic Patch Cord, singlemode, 1.8 mm zipcord, LC/PC to LC/PC duplex tuned, 3 m**

Product Classification

Portfolio	NETCONNECT®
Product Type	Fiber patch cord, duplex
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Type	OS1
Total Fibers, quantity	2
Jacket Color	Yellow
Fiber Mode	Singlemode

Dimensions

Cord Length	3.00 m 9.84 ft
Diameter Over Jacket	1.80 mm 0.07 in

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
---------------------	-------------------------------

General Specifications

Interface, connector A	LC
Interface, connector B	LC
Color, boot A	Blue
Color, boot B	Blue
Color, connector A	Blue
Color, connector B	Blue
Connector A, quantity	2
Connector B, quantity	2
Package Quantity	1
Polarity	Pairs flipped
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard

Optical Performance

Insertion Loss, maximum	0.30 dB
Return Loss, minimum	45.0 dB

6536501-3

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant