



E42399-000 | FIST-GPST-12-APL1-2

FIST GPST Fiber Patch/Splice Tray, 24 ports, LC/UPC, singlemode, SMOUV splice chip, 19 in, gray, right patch cord routing

Product Classification

Brand	FIST™
Product Series	FIST-GPST
Product Type	Fiber patch/splice tray
Regional Availability	EMEA

Body Features

Chassis Color	Gray
---------------	------

Configuration Features

Front Connector Type	LC/UPC
Number of Ports	24
Splice Chip Type	SMOUV
Configuration	Adapters and Splice Trays

Dimensions

Depth	190.00 mm 7.48 in
Height	18.00 mm 0.71 in
Width	355.00 mm 13.98 in

Operation/Application

For Use With	FIST-GPS Fiber Panels
--------------	-----------------------

Packaging Features

Included	Installation Instruction Mounting hardware
Packaging Method	Box/Carton
Packaging Quantity	1

Product Type Features

Optical Mode	Singlemode
Orientation	Right

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant