



760060905 | CAT 3 50 Port Panel  
Category 3 U/UTP High Density Voice Patch Panel, 50 port

## **OBSOLETE**

This product was discontinued on: December 1, 2016

### Replaced By

1711214-2	Telephone Patch Panel, category 3, RJ45, 19 in, 50-port, black
1711214-3	Telephone Patch Panel, category 3, RJ45, 19 in, 50-port, gray

## Product Classification

Portfolio	SYSTIMAX®
Product Type	Copper patch panel
Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Dimensions

Depth	139.70 mm   5.50 in
Height	44.45 mm   1.75 in
Width	482.60 mm   19.00 in

## Electrical Specifications

ANSI/TIA Category	3
Current Rating	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1000 Vac @ 60 Hz

## Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
-----------------------	--------------------------------------

## General Specifications

Intelligence Type	Passive
Total Ports, quantity	50
Cable Type	U/UTP (unshielded)
Brand	SYSTIMAX®
Color	Black
Ordering Note	Available in Europe, the Middle East and Africa
Package Quantity	1
Rack Type	EIA 19 in
Rack Units	1

## Mechanical Specifications

760060905 | CAT 3 50 Port Panel

Rear Termination Contact Plating	Nickel
Rear Termination Type	IDC

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system