



PANDUIT PART NUMBER		WIRE SIZE AWG	DIMENSIONS in.				HOUSING COLOR
PREFIX	PK		A $\pm .03$ ($\pm .8$)	B DIA. $\pm .01$ ($\pm .3$)	C $\pm .02$ ($\pm .3$)	D DIA. ($\pm .3$)	
PV18-P47	-CY -MY	22-18 (1.5-1.0)	.97 (24.6)	.07 (1.8)	.49 (12.4)	.15 (3.8)	RED
PV14-P47	-C -M	16-14 (1.5-2.5)	.97 (24.6)	.07 (1.8)	.49 (12.4)	.17 (4.3)	BLUE
PV10-P55*	-LY -DY	12-10 (4.0-6.0)	1.10 (27.9)	.10 (2.5)	.55 (14.0)	.25 (6.35)	YELLOW

NOTES:

- RECOMMENDED FOR:
A. SOLID OR STRANDED COPPER WIRE
- MATERIAL:
A. STAMPING - COPPER, TIN PLATED
B. HOUSING - VINYL, COLOR CODED
- PACKAGE QTY: STD. PKG. -LY=50, -C, -CY=100
BULK PKG. -DY=500, -M, -MY=1000
- DIMENSIONS IN BRACKETS ARE IN mm or mm²
- Tools:
PANDUIT APPROVED: CT-100, CT-160,
CT-550CH, CT-500CH
(EXCEPT PV10-P55)CT-1550, CT-1551
- WIRE STRIP LENGTH $5/16^{+1/32}_{-0}$ (7.9^{+.8}₋₀)

* Not UL Listed

LISTED
587H
E52164**PANDUIT** CORP.

TINLEY PARK, ILLINOIS

VINYL INSULATED PIN TERMINAL

REV	DATE	BY	CHK	DESCRIPTION	DRAWN BY	CHK'D	SCALE	DRAWING NO.
11	6/11	SRB		Added asterisk for PV10-P55 *Not UL Listed	DAW	RLS	NONE	A41335