

2.25
[57.2]

1.22
[31.0]

PANDUIT PART NUMBER *	"A" IN. / [mm]	WEIGHT lbs. / 10 pcs [g] / 10 pcs	MAXIMUM CABLE DIA. IN. [mm]	RECM'D FASTNER
BR2-1.3-A-_-	1.35 [34.3]	1.36 [617]	2.00 [50.8]	
BR2-1.3-_-	1.32 (33.5)	1.34 (607)		1/4" OR 6mm

4.88
[123.9]
(REF)

2.12
[53.8]

"A"

2.50
[63.5]

TEAR-TAB

ADHESIVE BACKED
BR2-1.3-A-

ADHESIVE BACKED
BR2-1.3-A-

CAD FILENAME/LAYERS

PANDUIT

CORP.

2 IN. BUNDLE RETAINER
[BR2-1.3-_-_-]

DRAWN BY JAD

JAD

MAT'LE

DATE 10-1-88

[illegible]

SCALE	NONE
-------	------

DRAWING NO.

GB2140BB

A

4	7/21/03	JAD		REVISED MATERIAL	08214088	4			
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP		