


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	MATERIAL	MARKER SIZE inches (mm)	LABELS PER ROW	STANDARD PKG. QTY.	COLOR
C100X038KBT	GMK4	1.000 0.375 X X ( 25.4 ) ( 9.52 )	3	10000	WHITE
C100X038KCT	GMK4				AMBER
C100X038TJT	GMT4-W				WHITE
C100X038YJT	GMY4-W				WHITE
C100X038CBT	GMC4				WHITE



**3** NOTES:  
1. MILLIMETER ARE IN ( ).

CAD FILENAME/LAYERS 100472HZ\_DC\_C10449/00D

**PANDUIT** CORP. TINLEY PARK, ILLINOIS

CUSTOMER DRAWING  
OPTIMUM C100X038\*\*T  
THERMAL TRANSFER LABELS

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
3	1/5/09	RVU		REMOVE NOTE 1. .12, .062, .020 WAS .030, .015, .010. ADD +/- .062.	5631		R	
2	5/21/07	RVU		ADDED NEW P/N, C100X038TJT, C100X038YJT AND C100X038CBT.	5002		R	
1	4/16/07	RVU		ADDED P/N: C100X038KCT. C100X038KBT, MAT'L SHOULD BE GMK4.	4954		R	
0	8-23-06	RVU		DRAWING RELEASE.	0000		R	

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:  
(.X) ± .12 (.XXX) ± .020  
(.XX) ± .062 ANGLES ±

**3**

UNLESS OTHERWISE SPECIFIED,  
ALL DIMENSIONS ARE GIVEN  
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY  
RVU

MAT'L:

SCALE  
NTS

DATE  
8-23-06

SEE TABLE

DRAWING NO.

C10449

DWG  
A  
SIZE

CHK'D