


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

4

PART NO.	MATERIAL	MARKER SIZE inches [mm]	LABELS PER ROW	STANDARD PKG. QTY.
C075X025YJT	GMY4 - W	0.750 X 0.250 [19.1] X [6.35]	3	10000
C075X025KBT	GMK4			
C075X025KCT				
C075X025CBT	GMC4			
C075X025YMT	GMY4 - S			
C075X025PBT	GMP4 - W			

4



NOTE:
1. SEE MFG. DWG. NO. A61226.
2. MILLIMETER ARE IN [].

CAD FILENAME/LAYERS 100472HF_C10263_C075X025xxT_04.PRT	
 PANDUIT CORP. TINLEY PARK, ILLINOIS	
CUSTOMER DRAWING OPTIMUM C075X025**T THERMAL TRANSFER LABELS	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .031 (.XXX) ± .010 (.XX) ± .015 ANGLES ±	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.
DRAWN BY RVU	MAT'L: SEE TABLE
DATE 9-30-04	SCALE NTS
CHK'D	DRAWING NO. C10263
	DWG SIZE A

4	10/22/07	RVU		GMY4-S WAS GMY4-HTS.	5188	R			
3	5/17/07	RVU	DAPE	ADDED NEW P/N, C075X025YMT AND C075X025PBT.	5003	R			
2	4/13/07	RVU	DWY	ADDED P/N: C075X025KCT, C075X025KBT, MATERIAL SHOULD BE GMK4.	4948	R			
1	3-31-06	RVU	DWY	ADDED "CUSTOMER DRAWING" ON TITLE. .750 WAS .800.	4435	R			
0	9-30-04	RVU	DWY	RELEASED TO PRODUCTION.	0000	R			
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	