



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
C4PPLK	.10 LB/10 PCS (46.2 g/10 PCS)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN [] ARE IN METRIC.
4. MATERIAL:
LABEL - VINYL
LABEL COVER - PETG
5. PART INCLUDES:
6 - LABEL
6 - LABEL COVER



PART NUMBER		C4PPLK	
TITLE			
4 POSITION FACEPLATE PATCH PANEL LABEL KIT			
CUSTOMER DRAWING			
ITEM REVISION NAME		M00742EP/00	
DATASET FILE NAME		M00742EP_DC/00A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		PANDUIT	
.x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °			
THIRD ANGLE PROJECTION		DRAWING NUMBER: 00742-87	
DRAWN BY	DATE	CHK	SCALE
JSP	7-30-01	MJD	NONE
SHT 1 OF 1			A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
1	3/6/14	JSP	REFR	MMR	A. REVISED DRAWING TITLE BLOCK.	00742-87
R	7-30-01	JSP	MJD	MJD	RELEASED TO PRODUCTION	00742-87