





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

A

PANDUIT PART#	COLOR	DESCRIPTION	WEIGHT
CC5E88BL	BLACK	MINI-COM CAT5e COUPLER MODULE	1.32 LB/100 PCS (600g/100 PCS)
CC5E88IW	INT. WHITE		
CC5E88GR	GREEN		
CC5E88BU	BLUE		
CC5E88OR	ORANGE		




COUPLER MODULE




NOTES:

- CATEGORY 5e/CLASS D 8-POSITION FEMALE-TO-FEMALE COUPLER MODULE.
- MATERIAL:  
MODULE HOUSING - UL94-V0 ABS  
MODULE CIRCUIT BOARD - GLASS REINFORCED EPOXY RESIN  
MODULE CONTACT CARRIER - UL94-V0 ABS
- DIMENSIONS IN PARENTHESES ARE IN METRIC.
- COMPATIBLE WITH ALL PANDUIT MINI-COM FACEPLATES AND MODULAR PATCH PANELS. NOT COMPATIBLE WITH SURFACE MOUNT BOXES.
- ACTS AS A SINGLE CONNECTOR IN CATEGORY 5e/CLASS D CHANNELS
- c(UL)US LISTED-UL FILE NUMBER E129886
- ALSO AVAILABLE AS 24-PORT COUPLER PATCH PANEL, PART NUMBER CP245E88BLY.



FRONT



REAR

ACTUAL SIZE

PART NUMBER		CC5E88**	
TITLE			
MINI-COM CAT5E COUPLER MODULE		CUSTOMER DRAWING	
ITEM REVISION NAME			
M02037CD/02		<b>PANDUIT</b>	
DATASET FILE NAME			
M02037CD_DC11/02A		MATERIAL:	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		SEE NOTE 2	
.x ± .1 [ 2.54 ]      .xxx ± .005 [ .127 ]		DRAWING NUMBER: 02037-11	
.xx ± .01 [ .25 ]      ANGLES ± 5 °			
THIRD ANGLE PROJECTION		DRAWING NUMBER:	
02037-11		SHT 1 OF 1	
DRAWN BY	DATE	CHK	SCALE
MDJr	12-21-04	CEF	FULL
REV	DATE	BY	CHK
APR			
DESCRIPTION		ECN	
		A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
4	6-20-14	MDJR	REFR	EJH	A. ADDED PART NUMBERS FOR GREEN, BLUE, AND ORANGE COLORS.	02037-11
3	2-3-14	BJN	EJH	EJH	UPDATED	02037-11

2

1

D10100DA/14