




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
CFG2**	.23 LB/10 PCS (106 g/10 PCS)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. (2) #6-32 X 1" PANHEAD SCREWS ARE SUPPLIED



PART NUMBER		PRODUCT SPEC/PKG SPEC	
CFG2**		N/A	
I.T. NUMBER		WORK INSTRUCTION	
N/A		N/A	
TITLE			
"GFCI" MODULE FRAME TWO POSITION			
CUSTOMER DRAWING			
ITEM REVISION NAME			
M00021CA/02.PRT			
DATASET FILE NAME		MATERIAL : ABS	
M00021CA_DC04/02A.PRT			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		DRAWING NUMBER: 00021 - 04	
.x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES : 5 °			
		THIRD ANGLE PROJECTION	
DRAWN BY	DATE	CHK	SCALE
RCA	7-28-97	CEF	NONE
		SHT 1 OF 1	
		SIZE	
		A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
4	11-6-12	BJN	JSP	JSP	A. UPDATED FORMAT TO REFLECT CURRENT PANDUIT LOGO REVISED & REDRAWN PREVIOUS REVS REMOVED FOR CLARITY	00021-04