


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	DESCRIPTION	WEIGHT
CJ64XX**Y	6 POSITION, 4 WIRE TERMINATION CAP	1.62 lb/100 PCS. [738 g/100 PCS.]
CJ66XX**Y	6 POSITION, 6 WIRE TERMINATION CAP	1.62 lb/100 PCS. [738 g/100 PCS.]
CJ66UXX**Y	6 POSITION, 6 WIRE MODULAR JACK TERMINATION CAP IS COLOR CODED FOR USOC WIRING SCHEME	1.62 lb/100 PCS. [738 g/100 PCS.]



NOTE:

- SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
- MATERIAL:
JACK HOUSING - ABS
NOMINAL WALL THICKNESS .078[2.0].
TERMINATION CAP - POLYCARBONATE.
- THIS PART IS DESIGNED FOR USE WITH MINI-COM PLATES AND BOXES.
- MEETS ALL CATEGORY 3 PERFORMANCE REQUIREMENTS AS DEFINED BY EIA/TIA.
- DIMENSIONS IN PARENTHESIS ARE IN METRIC.

PART NUMBER		CJ64XX**Y, CJ66XX**Y, CJ66UXX**Y	
TITLE			
MINI-JACK CATEGORY 3 TWISTED PAIR CONNECTOR		CUSTOMER DRAWING	
ITEM REVISION NAME		M02479NJ/00	
DATASET FILE NAME		M02479NJ_DC349/00B	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.x ± .xxx ± .010 [.3]		SEE NOTES	
.xx ± .03 [.8]		DRAWING NUMBER:	
THIRD ANGLE PROJECTION		02479-349	
DRAWN BY	DATE	CHK	SCALE
NER	3-25-06	WJC	NONE
SHT 1 OF 1		A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
1	3-25-06	JSP	REFR	EJH	A. REVISED DRAWING TITLE BLOCK.	02479-349
R	3-25-06	NER	WJC	WJC	RELEASED TO PRODUCTION	02479-349

D10100DA/14