


2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PART#	COLOR	DESCRIPTION	WEIGHT*
CJSH5E88TG**Y CJSH688TG**Y	BLACK RED BLUE GREEN VIOLET YELLOW	8 POSITION, 8 WIRE SHIELDED MODULE WITH INTEGRAL SHIELD. TERMINATION CAP IS COLOR CODED FOR T568A AND T568B WIRING SCHEMES.	3.314 LB/100 PCS (1503g/100 PCS)



*WEIGHT IS APPROXIMATE
**JACK COLOR SUFFIX

NOTES:

1. RED WIRE CAP DESIGNATES CATEGORY 5E PERFORMANCE.
2. WHITE WIRE CAP DESIGNATES CATEGORY 6 PERFORMANCE.
3. MATERIAL:
MODULE HOUSING- ABS
SHIELD - TIN PLATED PHOS. BRONZE.
WIRE CAP/CLIP -ZINC AND PC
4. ALL CATEGORY 5E & 6, 8 POSITION, 8 WIRE JACK MODULES ARE UNIVERSAL IN DESIGN. THEY ACCEPT SIX AND EIGHT POSITION MODULAR PLUGS WITHOUT DAMAGE.
5. DIMENSIONS IN PARENTHESES ARE IN METRIC.
6. .187 x .010" GROUNDING TAB PROVIDED AS OPTIONAL CONDUCTIVE PATH FOR GROUNDING.
7. ONLY THE 6 COLORS LISTED IN THE TABLE ARE AVAILABLE.
8. SHUTTER DOOR OPENS AND CLOSES AUTOMATICALLY WITH PLUG INSERTION AND REMOVAL.
9. SHUTTER DOOR PREVENTS THE ACCUMULATION OF DUST PER IP-40 PROTECTION RATING STANDARDS.



ACTUAL SIZE



PART NUMBER		SEE TABLE	
TITLE		MINI-COM CAT5E & CAT6 STP SPRING SHUTTERED JACK MODULE	
CUSTOMER DRAWING			
ITEM REVISION NAME		14M542AF/02	
DATASET FILE NAME		14M542AF_DC02/02A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)			
.X ±		SEE NOTES	
.XX ±		DRAWING NUMBER: 14M542AF-02	
THIRD ANGLE PROJECTION			
DRAWN BY	DATE	CHK	SCALE
BJN	5-29-15	ROJC	FULL
SHT 1 OF 1		A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
2	2-16-17	ROJC	NAGL	TMBA	B. MODEL REVISION UPDATED	14M542AF-02
1	11-10-15	BJN	ROJC	FMS	A. UPDATED DWG TO SHOW STRAIN RELIEF CLIP AS PART OF WIRE CAP	14M542AF-02
R	5-29-15	BJN	ROJC	FMS	RELEASED TO PRODUCTION	14M542AF-02

2

1