



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
CMF**	.17 LB/10 PCS (78 g/10 PCS)

NOTES:

- SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
- DIMENSIONS IN PARENTHESES ARE IN METRIC.



PART NUMBER		CMF**	
TITLE			
MINI-COM 3GHz F-TYPE COUPLER MODULE			
CUSTOMER DRAWING			
ITEM REVISION NAME		M01557AA/01	
DATASET FILE NAME		M01557AA_DC04/01A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]		MATERIAL:	
.x ± .03 [ .8 ]		MODULE BASE: ABS	
.xxx ± .010 [ .3 ]		COUPLER: NICKEL	
ANGLES ±		PLATED BRASS	
THIRD ANGLE PROJECTION		DRAWING NUMBER:	
01557-04		SHT 1 OF 1	
DRAWN BY	DATE	CHK	SCALE
JSP	3-16-04	JCO	NONE
REV	DATE	BY	CHK
2	1-20-17	MDJR	NAGL
1	6/10/14	JSP	REFR
R	3-16-06	JSP	JCO
APR	DESCRIPTION		ECN
	B. UPDATED DRAWING WITH NEW MODEL.		01557-04
	A. REVISED DRAWING TITLE BLOCK.		01557-04
	RELEASED TO PRODUCTION		01557-04

D10100DA/14