



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

1. SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
3. PART NUMBERS: SEE SHEET 2 FOR ALL PART NUMBERS.
4. CASSETTE WIRING COMPLIES WITH ANSI/TIA-568-C.0 SEE ANSI/TIA-568-C.0 FOR POLARITY DETAILS AND AN EXAMPLE OF A BASIC LINK.
5. CASSETTE WEIGHT: 6.3oz (178g)



FIBER POSITION FROM LC END TO MPO END													
METHOD A 24F - CASSETTE (AS)													
LC PORT NUMBER	MPO #1						MPO #2						
	1	2	3	4	5	6	7	8	9	10	11	12	
MPO FIBER POSITION	B	A	B	A	B	A	B	A	B	A	B	A	
	1	2	3	4	5	6	7	8	9	10	11	12	
METHOD A FLIPPED 24F - CASSETTE (AF)													
LC PORT NUMBER	MPO #1						MPO #2						
	1	2	3	4	5	6	7	8	9	10	11	12	
MPO FIBER POSITION	B	A	B	A	B	A	B	A	B	A	B	A	
	1	2	3	4	5	6	7	8	9	10	11	12	
METHOD B 24F - CASSETTE (BN)													
LC PORT NUMBER	MPO #1						MPO #2						
	1	2	3	4	5	6	7	8	9	10	11	12	
MPO FIBER POSITION	B	A	B	A	B	A	B	A	B	A	B	A	
	12	11	10	9	8	7	6	5	4	3	2	1	

00	09-16-16	SAT	TMSE	EJH	RELEASED TO PRODUCTION	12F187MG-DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

TITLE		HD FLEX CASSETTE, 12-PORT DUPLEX LC TO (2) 12-FIBER MPO	
ITEM REVISION NAME		CUSTOMER DRAWING	
DATASET FILE NAME		12F187MG/02	
MATERIAL:		12F187MG_DC/02A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		.x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °	
DRAWING NUMBER:		THIRD ANGLE PROJECTION	
DRAWN BY		SCALE	
DATE		SHT 1 OF 2	
CHK		SIZE	
SAT		A	

