



2


1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




NOTES:


1. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
2. DIMENSIONS IN BRACKETS ARE METRIC.
3. ENCLOSURE MATERIAL: GALVANNEALED STEEL
ENCLOSURE COLOR: BLACK
4. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
5. PART WEIGHT 0.6 lbs (0.27 kg)





FLEX-ORUCH04



FLEX-ORUCH06



FLEX-ORUCH12

							TITLE HD FLEX ORU CASSETTE HOLDER					
							CONTROL DRAWING					
							ITEM REVISION NAME 15F318AH/01					
							DATASET FILE NAME 15F318AH_DC/01A					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] DIMENSIONS ARE FOR REFERENCE ONLY				PART NO: FLEX-ORUCH**	
											THIRD ANGLE PROJECTION	
01	10-04-16	SAT	BONS	TMK	RELEASED TO PRODUCTION	15F318AH-DC						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY BONS	DATE 8-9-16	CHK SAT	SCALE 1:4	SHT 1 OF 1	SIZE A

2

1