


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NUMBER	DESCRIPTION
FVFLPC-1.25SMY	VFL SM 1.25mm UNIVERSAL PATCHCORD

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE PACKAGE QUANTITY.
2. CONSTRUCTED WITH 9/125 MICRON SINGLEMODE CABLE AND A ZIRCONIA SPLIT SLEEVE.
3. EXTRA SPLIT SLEEVES ARE PROVIDED AS REPLACEMENTS.
4. PATCHCORD LENGTH IS 20.3 cm [8"].
5. ALL MATERIALS AND COMPONENTS USED MUST MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTIONS OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.

TETHERED DUSTCAP
(2 SUPPLIED)

INTERFACE
FOR CONNECTION TO PRE-POLISHED
CONNECTOR WITH 1.25mm FERRULE

ST CONNECTOR
FOR CONNECTION TO V.F.L. UNIT

PART NUMBER		FVFLPC-1.25MY						
TITLE								
VFL SM 1.25mm UNIVERSAL PATCHCORD		CUSTOMER DRAWING						
ITEM REVISION NAME		M01893AL/01	PANDUIT					
DATASET FILE NAME		M01893AL_DC-Y/01C						
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		MATERIAL:						
.X ±	.XXX ±	DRAWING NUMBER: 01893-58						
.XX ±	ANGLES ±							
THIRD ANGLE PROJECTION								
DRAWN BY	DATE	CHK	SCALE					
MC	12-15-04	MMW	NONE					
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	SHT 1 OF 1	SIZE
3	11/18/15	JSP	WJM	RWB	A. UPDATED DRAWING TITLE BLOCK.	01893-58		A

D10100DA/14