


PART NO.	"A" (IN.) MIN.	"B" (IN.) ±0.062	"C" +/- .062 (IN.)	MATERIAL	COLOR	PART NO.	"A" (IN.) MIN.	"B" (IN.) ±.062	"C" +/- .062 (IN.)	MATERIAL	COLOR
T100X000YK1	1200	1.00	0.125	GMV4-C	CLEAR	T200X000VSIY	1200	2.00	0.125	GMV14	GREEN
T200X000VRIY	1200	2.00	0.125	GMV14	BROWN	T200X000VUIY	1200	2.00	0.125	GMV14	ORANGE
T200X000YK1	1200	2.00	0.125	GMV4-C	CLEAR	T200X000VWIY	1200	2.00	0.125	GMV14	RED
T225X000YK1	1200	2.25	0.125	GMV4-C	CLEAR	T200X000VXIY	1200	2.00	0.125	GMV14	YELLOW
T400X000VRIY	1200	4.00	0.125	GMV14	BROWN	T400X000VYIY	1200	4.00	0.125	GMV15	BLACK
T400X000YK1	1200	4.00	0.125	GMV4-C	CLEAR	T400X000VTIY	1200	4.00	0.125	GMV14	GRAY
T425X000YK1	1200	4.25	0.125	GMV4-C	CLEAR	T400X000VVIY	1200	4.00	0.125	GMV15	PURPLE
T100X000VPIY	1200	1.00	0.125	GMV14	WHITE	T400X000VPIY	1200	4.00	0.125	GMV14	WHITE
T100X000VUIY	1200	1.00	0.125	GMV14	ORANGE	T400X000VQIY	1200	4.00	0.125	GMV15	BLUE
T100X000VXIY	1200	1.00	0.125	GMV14	YELLOW	T400X000VSIY	1200	4.00	0.125	GMV14	GREEN
T100X000VQIY	1200	1.00	0.125	GMV15	BLUE	T400X000VUIY	1200	4.00	0.125	GMV14	ORANGE
T100X000VSIY	1200	1.00	0.125	GMV14	GREEN	T400X000VWIY	1200	4.00	0.125	GMV14	RED
T100X000VWIY	1200	1.00	0.125	GMV14	RED	T400X000VXIY	1200	4.00	0.125	GMV14	YELLOW
T100X000VYIY	1200	1.00	0.125	GMV15	BLACK	T200X000Y2T	180	2.00	0.125	GMV4-HT	WHITE/GREEN
T200X000VYIY	1200	2.00	0.125	GMV15	BLACK	T400X000Y2T	180	4.00	0.125	GMV4-HT	WHITE/GREEN
T200X000VTIY	1200	2.00	0.125	GMV14	GRAY						
T200X000VVIY	1200	2.00	0.125	GMV15	PURPLE						
T200X000VPIY	1200	2.00	0.125	GMV14	WHITE						
T200X000VQIY	1200	2.00	0.125	GMV15	BLUE						



NOTES:
1. RESIN RIBBON
RECOMMENDED.

CAD FILENAME/LAYERS		100472ER-DC-C10274/11H	
PANDUIT		CORP. TINLEY PARK, ILLINOIS	
THERMAL TRANSFER CONTINUOUS TAPES			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .12 (.XXX) ± .025 (.XX) ± .062 ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
7	6/21/12	RVU	CHANGE GMV15 INSTEAD OF GMV14 (for the black and purple parts only).
6	5/7/12	RVU	GMV14 CHANGES TO GMV15.
REV	DATE	BY	CHK
DESCRIPTION		ECN - R	CUST SUP
DRAWN BY		RVU	MAT'L:
DATE		10-25-06	SEE TABLE
CHK'D			
SCALE		NTS	
DRAWING NO.		C10274	
DWG		A	
SIZE			