


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBERS	LEGEND [each]	MARKERS PER WAND	MARKERS PER PKG.	STD. PKG. QTY.	STD. CTN. QTY.	WIRE SIZE RANGE
PCA23-A THRU PCA23-Z	'A' THRU 'Z'	20	60	1	10	.23" - .37"
PCA23-A-D	'A' - 'D' [1 EA.]	20	80	1	10	.23" - .37"
PCA23-E-H	'E' - 'H' [1 EA.]	20	80	1	10	.23" - .37"
PCA23-I-L	'I' - 'L' [1 EA.]	20	80	1	10	.23" - .37"
PCA23-M-P	'M' - 'P' [1 EA.]	20	80	1	10	.23" - .37"
PCA23-Q-T	'Q' - 'T' [1 EA.]	20	80	1	10	.23" - .37"
PCA23-U-X	'U' - 'X' [1 EA.]	20	80	1	10	.23" - .37"
PCA23-Y-Z	'Y', 'Z', '-', '+'	20	80	1	10	.23" - .37"
PCA23-0 THRU PCA23-9	'0' THRU '9'	20	60	1	10	.23" - .37"
PCA23-0-3	'0' - '3' [1 EA.]	20	80	1	10	.23" - .37"
PCA23-4-7	'4' - '7' [1 EA.]	20	80	1	10	.23" - .37"
PCA23-8-9	'8', '9', '+', '-'	20	80	1	10	.23" - .37"
PCA23-MIN	'-'	20	60	1	10	.23" - .37"
PCA23-PLS	'+'	20	60	1	10	.234" - .367"

NOTES:

- COLOR: WHITE WITH BLACK LEGENDS.
- MILLIMETERS ARE IN [].
- ONE SIDE PRINTED.

5



PCA23-* CLIP-ON WIRE MARKER


CUSTOMER DRAWING

ITEM REVISION NAME

I00281DD/06

DATASET FILE NAME

I00281DD_DC_C10514/06F

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE: IN [mm].x ± .12 [3.05] .xxx ± .025 [.635]
.xx ± .062 [1.57] ANGLES ±THIRD ANGLE
PROJECTION

MATERIAL:

WHITE MARKER-ACETAL

DRAWING NUMBER:

C10514

DRAWN BY

DATE

CHK

SCALE

SIZE

RVU

9/12/06

JM

NTS

SHT 1 OF 1

A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
5	10/27/15	RVU	SEWH	JHAC	ADD NOTE 3 TO SHOW ONE SIDE PRINTED.	GAECN03229
4	4/22/13	RVU	SEWH	JHAC	CHANGE OLD DRAWING BOARDER TO NEW PANDUIT DRAWING BOARDER.	GAECN02988
3	3/28/11	RVU			UPDATE ON TABLE, NOTES, & TOLERANCES. CHG. FROM B TO A FORMAT. UPDATE TABLE.	6336
2	8/11/10	RVU			ADDED TOLERANCES AND NOTE 1 THRU 5. ADDED PART NUMBERS.	6079
1	10/6/06	RVU			ADDED TOLERANCE AND REVISED TABLE.	4716
0	9/12/06	RVU			DRAWING RELEASE.	4677

B

A

A

A

A

A