


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PART NO.	* "A" +/- .06	LEGEND	Total Markers Each Legend per Book	STD. PKG. BOOK (S)	STD. CTN. BOOK (S)	TOTAL PAGES PER BOOK
PCMB-1 PCMBR-1	0.217	0 THRU 9	45	1	10	10
PCMB-2 PCMBR-2	0.217	A THRU Z, 0 THRU 15, +, -, /	10	1	10	10
PCMB-3 PCMBR-3	0.217	1 THRU 45	10	1	10	10
PCMB-4 PCMBR-4	0.217	1, 2, 3	150	1	10	10
PCMB-5 PCMBR-5	0.217	A, B, C	150	1	10	10
PCMB-6	0.217	T1, T2, T3	150	1	10	10
PCMB-7	0.217	L1, L2, L3	150	1	10	10
PCMB-8	0.217	1 THRU 15	6	1	10	10
		16 THRU 90	4	1	10	10
PCMB-9	0.217	A THRU Z, +, -, /, 0	2	1	10	10
		1, 2, 3, A, B, C	45	1	10	10
PCMB-10	0.217	L1, L2, L3, T1, T2, T3	30	1	10	10
		Solid NEMA colors red, yellow, white, light blue, light green, black, brown, orange, gray, dark green	45	1	10	10
PCMB-11	0.217	1 THRU 30	15	1	10	10
PCMB-12	0.217	A THRU Z	15	1	10	10
		+	8	1	10	10
		-	7	1	10	10
PCMB-13	0.434	.464 NO LEGEND, Blank (write-on)	21	1	10	10
		+, -, AC, DC	45	1	12	12
		P.N.G.	21			
PCMB-14	0.217	SPARE, BLANK (WRITE-ON)	10	1	10	10
		46 THRU 90	10	1	10	10
PCMB-15	0.217	"0", "+", "-"	15	1	10	11
		"1" THRU "45"	1			
PCMB-16	0.217	0 THRU 33, A, B, C, +, -, L1, L2, L3, T1, T2, T3	10	1	10	10
PCMB-25	0.217	0 THRU 9	45	1	10	12
		L1, L2, L3, T1, T2, T3	15	1	10	

NOTE:  
1. MILLIMETERS ARE IN [ ].

CAD FILENAME/LAYERS 100414BA-DC-C10607/05D

PANDUIT CORP. TINLEY PARK, ILLINOIS

CUSTOMER DRAWING  
PCMB-\*, PCMBRS-\*  
BOOK PAGE

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
3	1/19/10	RVU		0.434 WAS 0.295, 0.361, & 0.464. P.N.G. WAS POS, NEG, GND. 21 WAS 33, & 27. 12 WAS 10. FOR PCMB-13 ONLY.	5947	R		
2	11/2/09	RVU		REVISED ON PCMB-15, 15 WAS 10. 11 WAS 10.	5900	R		
1	8/20/09	RVU		UPDATE TABLES. FOLLOW WITH THE CATALOG. TOLERANCES INCORRECT. .12, .062, .025 WAS .03, .015, .010.	5771	R		
0	8/2/07	RVU		DRAWING RELEASE.C10607 R	5099	R		

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:  
(.X) ± .12 (.XXX) ± .025  
(.XX) ± .062 ANGLES ±

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY RVU

MAT'L:

SCALE NTS

DATE 8/2/07

GMC

DRAWING NO.

C10607

CHK'D

DWG A SIZE