


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




| PANDUIT PART# | DESCRIPTION | WEIGHT |
|---------------|---|-----------------------------------|
| NK6TM** | 8 POSITION, 8 WIRE UNIVERSAL MODULE. TERMINATION CAP IS COLOR CODED FOR T568A AND T568B WIRING SCHEMES. | 1.43 LB/100 PCS (649g/100 PCS) |



NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND PACKAGE QUANTITY.
2. MATERIAL:
MODULE HOUSING- ABS
NOMINAL WALL THICKNESS .078(2.0).
PRESERVATION CAP-PC
3. ALL NETKEY CAT6, 8 POSITION, 8 WIRE JACK MODULES ARE UNIVERSAL IN DESIGN. THEY ACCEPT SIX AND EIGHT POSITION PAIR MODULAR PLUGS WITHOUT DAMAGE.
4. THIS PART IS DESIGNED FOR USE WITH STANDARD KEYSTONE OPENINGS.
5. DIMENSIONS IN PARENTHESES ARE IN METRIC.

PANEL OPENING REQUIREMENTS
PANEL THICKNESS: .048" - .058"
(1.22mm - 1.47mm)



| | | | |
|--|---------|---|-------|
| PART NUMBER | | NK6TM** | |
| TITLE | | NETKEY CATEGORY 6 JACK MODULE | |
| CUSTOMER DRAWING | | | |
| ITEM REVISION NAME | | M01336EJ/00 | |
| DATASET FILE NAME | | M01336EJ_DC41/00B | |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) | | PANDUIT MATERIAL: SEE NOTE 2 | |
| .X ± .XXX ± .010 [.3] .XX ± .03 [.8] ANGLES ± | | | |
| THIRD ANGLE PROJECTION | | DRAWING NUMBER: 01336-41 | |
| DRAWN BY | DATE | CHK | SCALE |
| MDJR | 5-06-03 | REFR | NONE |
| SHT 1 OF 1 | | A | |

| REV | DATE | BY | CHK | APR | DESCRIPTION | ECN |
|-----|---------|------|------|-----|-------------------------|----------|
| 1 | 5-16-14 | MDJR | REFR | JCK | A. UPDATED TITLE BLOCK. | 01336-41 |
| R | 5-12-03 | MDJR | | | RELEASED TO PRODUCTION | 01336-41 |