





PANDUIT P/N	WEIGHT
PVQ-EPC28	0.2 LB EA. 92g EA.

NOTES:  
1. DIMENSIONS IN BRACKETS ARE IN METRIC.  
2. PART INCLUDES:  
(1) PANVIEW IQ EXPANSION PORT CABLE 28in (PVQ-EPC28)



MODEL FILENAME <b>m02676hb_rs485_01.sldprt</b>		SIZE <b>A</b>
DRAWING FILENAME <b>M02676HB_DC117_00A.slddrw</b>		
PanView iQ Expansion Port Cable, 28in/0.71m CUSTOMER DRAWING		
 THIRD ANGLE PROJECTION	 <b>PANDUIT</b> ™ CORP. TINLEY PARK, ILL 60477	I.L. NUMBER N/A
		PRODUCT SPEC/ PKG SPEC N/A
		ASSEMBLY METHOD/ TEST METHOD N/A
		SCALE NONE
ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03      (.XXX) ±.005 (.XX) ±.01      ANGLES ±1°		
DRAWN BY ALP	REVIEW DRAWING NUMBERS	PART NO. PVQ-EPC28
DATE 1/31/11		
CHK'D MJD	MAT'L:  SEE NOTES ABOVE	DRAWING NO. 02676-117 Sheet 1 of 1

R	1/31/11	ALP	MJD	RELEASE TO PRODUCTION	02676-117	MJD	MJD		
REV.	DATE	BY	CHK D	DESCRIPTION	ECN	ECN REV	CUS T	S U P	GM BH