




NOTES:
1. IDENTIFICATION: 1RU HORIZONTAL, (10) C-13, METERED
120V / 30A / SINGLE-PHASE POU

2. ACCESSORY COMPONENTS:
 - (4) 10-32 x 1/2" MOUNTING SCREWS
 - (4) 12-24 x 1/2" MOUNTING SCREWS
3. DIMENSIONS IN PARENTHESES ARE METRIC (mm).
4. POWER METER - RED, 4-DIGIT LED CONTINUOUSLY SCROLLS THROUGH POWER FACTOR, AMPS, VOLTS (RMS), AND REAL POWER IN WATTS (RMS).
5. UL® & c-UL® LISTED 1950.
6. RoHS COMPLIANT.
7. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
8. MAXIMUM AVAILABLE INPUT POWER = 2.9 KW
9. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.

PANDUIT P/N	WEIGHT
HB1A1M2BT10M1	6 lb (2.7 kg)



PLUG
30 AMP, 125V
TWIST-LOCK
NEMA L5-30P



TEN (10)
RECEPTACLES
15 AMP, 250V
STRAIGHT BLADE
IEC 60320/C13

01A	8-2-12	PIP	MRWA	A. UPDATED NOTE #8. B. ADDED NOTE #9.		09V098DK				
00A	2-24-11	MAV	KRKE	RELEASED TO PRODUCTION		09V098DK				
REV	DATE	BY	CHK	DESCRIPTION		ECN - R	CUST	SUP	OTH	

MODEL FILENAME		09V098DK/01.PRT	
CAD FILENAME/LAYERS		09V098DK_DC/01A.PRT	
 PANDUIT CORP TINLEY PARK, ILLINOIS			
1RU HORIZONTAL, (10) C-13, METERED POWER OUTLET UNIT CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED,	
INCHES X.X +/- 0.03 X.XX +/- 0.015 X.XXX +/- 0.005		[METRIC - MILLIMETER] X +/- 0.8 X.X +/- 0.4 X.XX +/- 0.13	
ANGLE +/- °		ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
DRAWN BY MAV		SCALE NONE	
DATE 2-24-11		DRAWING NO.	
CHK'D KRKE		09V098DK	
		DWG B SIZE	