

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
HB1D2J0AA10M1	2.3 lb (1.1 kg)

NOTES:

1. IDENTIFICATION: 1RU HORIZONTAL, (10) C-13, METERED
230V / 16A / SINGLE-PHASE POU

<u>PART NO.</u>	<u>COLOR</u>
HB1D2J0AA10M1	BLACK

2. ACCESSORY COMPONENTS:

(4) M6 x 20mm MOUNTING SCREWS
(4) 12-24 x 1/2" MOUNTING SCREWS
(1) RETAINING CLAMP FOR C-20 INLET

3. DIMENSIONS IN PARENTHESES ARE METRIC (mm).

4. POWER METER - RED, 4-DIGIT LED CONTINUOUSLY SCROLLS THROUGH POWER FACTOR, AMPS, VOLTS (RMS), AND REAL POWER IN WATTS (RMS).




5. UNIT COMPLIES WITH IEC 60950-1, EN55022, EN55024, C-TICK AND IS CE MARKED.

6. RoHS COMPLIANT.


7. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.

8. MAXIMUM AVAILABLE INPUT POWER = 3.7 KW

9. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.



C20 POWER INLET
20 AMP, 250V, SINGLE-PHASE
SOCKET
IEC320



TEN (10)
RECEPTACLES
10 AMP, 250V
STRAIGHT BLADE
IEC 60320/C13

01A	8-23-12	PIP	MRWA	C. REVISED NOTE #5.	09V098HE					
00B	2-15-12	MRWA	KRKE	B. ADDED NOTE 9 A. REPLACED #10-32 SCREW WITH M6 SCREW	09V098HE					
00A	2-10-11	MAV	KRKE	RELEASED TO PRODUCTION	09V098HE					
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH		

MODEL FILENAME		09V098HE/01.PRT	
CAD FILENAME/LAYERS		09V098HE_DC/01A.PRT	
 PANDUIT CORP TINLEY PARK, ILLINOIS			
1RU HORIZONTAL, (10) C-13, METERED POWER OUTLET UNIT CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED,	
INCHES X.X +/- 0.03 X.XX +/- 0.015 X.XXX +/- 0.005		[METRIC - MILLIMETER] X +/- 0.8 X.X +/- 0.4 X.XX +/- 0.13	
ANGLE +/- 1°		ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
DRAWN BY MAV		SCALE NONE	
DATE 2-10-11		DRAWING NO.	
CHK'D KRKE		09V098HE	
		DWG B SIZE	