


2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

# NOTES:

1. VISIT OUR ON-LINE CATALOG AT [WWW.PANDUIT.COM](http://WWW.PANDUIT.COM) FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. DIMENSIONS IN PARENTHESES ARE ENGLISH (in).
3. HEIGHT RANGE OF FLOOR SKIRT IS BETWEEN 25.4mm (1.0") AND 38mm (1.5") FROM THE FLOOR.
4. PARTS SUPPLIED:  
 (1)-SIDE SKIRT  
 (1)-LEFT HAND BRACKET  
 (1)-RIGHT HAND BRACKET  
 (2)-510mm PIECES OF FOAM  
 (1)-HARDWARE KIT



PANDUIT PART NUMBER	PAINT COLOR	WEIGHT
N2EORIBA1070B1	BLACK	.73 Kg/EACH 1.6 LBS/EACH
N2EORIBA1070W1	WHITE	.73 Kg/EACH 1.6 LBS/EACH
N2EORIBA1070G1	GREY	.73 Kg/EACH 1.6 LBS/EACH
N2EORICA1200B1	BLACK	.78 Kg/EACH 1.7 LBS/EACH
N2EORICA1200W1	WHITE	.78 Kg/EACH 1.7 LBS/EACH
N2EORICA1200G1	GREY	.78 Kg/EACH 1.7 LBS/EACH

						TITLE						
						N-TYPE END OF ROW FLOOR SKIRT						
						CUSTOMER DRAWING						
						ITEM REVISION NAME						
						12V343SE/00.PRT						
						DATASET FILE NAME						
						12V343SE_DC/00A.PRT						
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:						
						<div style="display: flex; justify-content: space-between;"> <div>                         </div> <div>           ANGLE +/- 1°         </div> </div>						
						MATERIAL/COLOR:						
						N/A						
						DRAWING NUMBER:						
						12V343SE-DC						
OOA	2-13-13	TWV	<i>PSC</i>	JDWE	RELEASED TO PRODUCTION	12V343SE-DC						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
							TWV	2-13-13		NONE		A

2

1