



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.





DETAIL A
(SCALE 2X)

PANDUIT P/N	WEIGHT
PL1A1D0BA08E1	10 lb (4.5 kg)



NETWORKED ETHERNET CONNECTION
(SEE DETAIL A)



PLUG
20 AMP, 125V, SINGLE-PHASE
TWIST LOCK
NEMA L5-20P

TEN (10)
RECEPTACLES
20 AMP, 125V
STRAIGHT BLADE
NEMA 5-20R

00A	8-26-11	PIP	RRKE	RELEASED TO PRODUCTION	09V098QX				
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH	

MODEL FILENAME		09V098QX/00.PRT	
CAD FILENAME/LAYERS		09V098QX_DC/00A.PRT	
 PANDUIT CORP TINLEY PARK, ILLINOIS			
1RU HORIZONTAL, (8) 5-20R SWITCHED WITH PER OUTLET POWER & ENVIROMENTAL MONITORED			
CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED,	
INCHES X.X +/- 0.03 X.XX +/- 0.015 X.XXX +/- 0.005		[METRIC - MILLIMETER] X, +/- 0.8 X.X +/- 0.4 X.XX +/- 0.13	
ANGLE +/- °		ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
DRAWN BY PIP		SCALE NONE	
DATE 8-26-11		DRAWING NO. 09V098QX	
CHK'D KRKE		DWG B	