





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	WEIGHT
PZICFK-E	7.0 LB/EACH 3.2 kg/EACH

- VISIT OUR ONLINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH PART.
- CONVERTS PASSIVE IN-CEILING ENCLOSURE (PZICE) TO AN ACTIVE IN-CEILING ENCLOSURE FOR EUROPEAN MARKETS.
- PART INCLUDES:
 - (1) SCHUKO 230 VOLT EXHAUST FAN ASSEMBLY
 - (1) AIR DAM
 - (1) FAN SCREEN PLATE
 - (1) SCHUKO ELECTRICAL JUNCTION BOX
 - (1) PACK OF (4) #10-32 X 3/8" SCREWS
 - (1) PACK OF (4) #6-32 X 1/4" SCREWS
- FAN RATING:
 - VOLTAGE: 230V AC
 - CFM: 61 CFM
 - CE MARKED FOR EU LVD



FAN SCREEN PLATE

SCHUKO ELECTRICAL JUNCTION BOX

MODEL FILENAME		V10447AE/02
CAD FILENAME/LAYERS		V10447AE_DC/02A
PANDUIT		CORP. TINLEY PARK, ILLINOIS
EUROPEAN FAN KIT (PZICFK-E)		CUSTOMER DRAWING
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.
INCHES X.X +/- 0.03 X.XX +/- 0.015 X.XXX +/- 0.005		[METRIC - MILLIMETER] X +/- 0.8 X.X +/- 0.4 X.XX +/- 0.13
DRAWN BY BAME		SCALE NONE
DATE 11-20-08		DRAWING NO. V10447AE-DC SHEET 1 OF 2
CHK'D BAME		MAT'L: SEE NOTES A SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
O2A	11-15-12	RYB	BAME	A: ADDED FAN RATING	V10447AE-DC				
O1A	11-20-08	BAME		RELEASED TO PRODUCTION	V10447AE-DC				

