


NOTES:
1. IDENTIFICATION: VERTICAL, MIXED (24) C-13 & (6) C-19, METERED
230V / 32A / SINGLE-PHASE POU

PANDUIT P/N	WEIGHT
VB1D2B2BM30P1	17 lb (7.7 kg)


2. ACCESSORY COMPONENTS:
- (4) M6 x 20mm MOUNTING SCREWS
 - (4) #12-24 x 1/2" MOUNTING SCREWS
 - (2) #10-32 LOCKING COLLAR SCREWS
 - (2) L-BRACKETS

3. DIMENSIONS IN PARENTHESES ARE METRIC (mm).


4. POWER METER - RED, 4-DIGIT LED CONTINUOUSLY SCROLLS THROUGH POWER FACTOR, AMPS, VOLTS (RMS), AND REAL POWER IN WATTS (RMS).
5. UNIT COMPLIES WITH IEC 60950-1, EN55022, EN55024, AND IS CE MARKED.
6. RoHS COMPLIANT.
7. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
8. MAXIMUM AVAILABLE INPUT POWER = 7.4 KW
9. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.




REAR VIEW




TOP VIEW




RIGHT SIDE VIEW



PLUG
32 AMP, 250V, SINGLE-PHASE
2P/3W
IEC 60309, SPLASHPROOF




TWENTY-FOUR (24)
RECEPTACLES
10 AMP, 250V
STRAIGHT BLADE
IEC 60320/C13



SIX (6)
RECEPTACLES
16 AMP, 250V
STRAIGHT BLADE
IEC 60320/C19

01A	8-15-12	PIP	MRWA	A. UPDATED NOTE #8. B. ADDED NOTE #9. C. UPDATED ALL VIEWS	09V098HG					
00A	2-10-11	MAV	KRKE	RELEASED TO PRODUCTION	09V098HG					
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH		

MODEL FILENAME		09V098HG/01.PRT	
CAD FILENAME/LAYERS		09V098HG_DC/01A.PRT	
 PANDUIT CORP TINLEY PARK, ILLINOIS			
VERTICAL, MIXED (24) C-13 & (6) C-19, METERED POWER OUTLET UNIT CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED,	
INCHES X.X +/- 0.03 X.XX +/- 0.015 X.XXX +/- 0.005		[METRIC - MILLIMETER] X +/- 0.8 X.X +/- 0.4 X.XX +/- 0.13	
ANGLE +/- °		ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
DRAWN BY MAV		SCALE NONE	
DATE 2-10-11		DRAWING NO. 09V098HG	
CHK'D KRKE		DWG B	