


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT PART # 	TAB SIZE		WIRE RANGE		COLOR	DIMENSIONS in. [mm]					TOOL CHART								
	ENGLISH in.	METRIC mm	ENGLISH AWG	METRIC mm ²		MAX. WIRE INSUL. DIA.	L ± .03 [0,8]	W ± .01 [0,3]	H ± .01 [0,3]	D ± .01 [0,3]	PRESSES: CP-861, CP-862, CP-871								
											APPLICATOR DIES: CA9, CA-800EZ								
DNFR18250FIB-KD	.250 X .032	6,3 X 0,8	22-18	0,5-1,0	RED		.178 [4,52]	.57 [14,5]	.37 [9,4]	.21 [5,3]	.60 [15,2]	CD-800-9 CD9-9C							
DNFR18205FIB-KD	.205/.187 X .032	5,2/4,8 X 0,8																	
DNFR18206FIB-KD	.205/.187 X .020	5,2/4,8 X 0,5																	
DNFR14250FIB-KD	.250 X .032	6,3 X 0,8	16-14	1,5-2,5	BLUE														
DNFR14205FIB-KD	.205/.187 X .032	5,2/4,8 X 0,8																	
DNFR14206FIB-KD	.205/.187 X .020	5,2/4,8 X 0,5																	

NOTES:

- USED FOR:
 - STRANDED COPPER WIRE ONLY
 - 221°F [105°C] MAX. OPERATING TEMPERATURE
 - 600V. MAX. BLDG WIRE
 - 6-12 LBS INITIAL INSERTION/WITHDRAWAL FORCE
- WIRE STRIP LENGTH:

11/32 ^{+1/32}/₋₀ [8,7 ^{+0,8}/₋₀]
- MATERIAL:
 - STAMPING: CDA 260 BRASS, TIN PLATED
 - HOUSING: TYPE 6/6 NYLON
- SEE www.panduit.com FOR PACKAGE QUANTITIES INDICATED BY PART NUMBER SUFFIX
- DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT
- CURL SLOTS: DNFR18205FIB, DNFR18206FIB, DNFR14205FIB, DNFR14206FIB ONLY.



										TITLE FEMALE DISCONNECTS, NYLON FULLY INSULATED - RIGHT ANGLE REEL SMART  CUSTOMER DRAWING				
										ITEM REVISION NAME N41124BA/11				
										DATASET FILE NAME N41124BA_DC/11 - A41124_REV11				
--	---	---	---	---	ADDED "REEL SMART" TO DRAWING TITLE.		----			UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± --- .XXX ± --- .XX ± --- ANGLES ± ---  THIRD ANGLE PROJECTION				
11	2/22/18	BWG	SKB	JADE	 REVISED DIMENSION LOCATION OF HOUSING WIDTH. REMOVED TITLE BLOCK TOLERANCES.		019464/00			MATERIAL: SEE NOTES				
10	10.10.12	JBN	LCA	VMB	ADDED METRIC EQUIVALENT. CHANGE PACKAGING NOTE. ADDED TOOLS CHART. UPDATED DRAWING TO CURRENT STANDARDS.		A41124			DRAWING NUMBER: A41124				
REV	DATE	BY	CHK	APR	DESCRIPTION		ECN	DRAWN BY MG	DATE -	CHK -	SCALE N.T.S.	SHT 1 OF 1	SIZE A	