




PPS PART NUMBER	"A" WIDTH in. [mm]	"B" HEIGHT in. [mm]	STD. PKG. QTY.
PPS0204	4.50 [114.3]	2.25 [57.2]	5
PPS0305	5.00 [127.0]	3.50 [88.9]	
PPS0507	7.00 [177.8]	5.00 [127.0]	
PPS0514	14.00 [355.6]	5.00 [127.0]	
PPS0410	10.00 [254.0]	4.00 [101.6]	
PPS0710	7.00 [177.8]	10.00 [254.0]	1
PPS1007	10.00 [254.0]	7.00 [177.8]	
PPS1014	14.00 [335.6]	10.00 [254.0]	
PPS1209	9.00 [228.6]	12.00 [304.8]	
PPS1420	20.00 [508.0]	14.00 [335.6]	



PVS PART NUMBER	"A" WIDTH in. [mm]	"B" HEIGHT in. [mm]	STD. PKG. QTY.
PVS0109	9.00 [228.6]	1.50 [38.1]	5
PVS0305	5.00 [127.0]	3.50 [88.9]	
PVS0404	4.00 [101.6]	4.00 [101.6]	
PVS0505	5.00 [127.0]	5.00 [127.0]	
PVS0507	7.00 [177.8]	5.00 [127.0]	
PVS0509	9.00 [228.6]	5.00 [127.0]	1
PVS0705	5.00 [127.0]	7.00 [177.8]	
PVS0710	10.00 [254.0]	7.00 [177.8]	

NOTES:

1. MILLIMETERS ARE IN [].
2. VISIT www.Panduit.com to view legend images.
3. REFERENCE C10950, C10951, C10949 FOR ADDITIONAL PPS AND PVS STYLES.

CAD FILENAME/LAYERS

I00824BR-DC-C10952/01B

PANDUIT CORP. TINLEY PARK, ILLINOIS

CUSTOMER DRAWING Safety Sign
PVS and PPS STYLE 1

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .06 (.XXX) ± .015
(.XX) ± .032 ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

2 4/7/2014 ZSG ADD PN: PPS0410 ON TABLE

1863

R

1 1/26/12 RVU ADD PN: PVS0705 ON TABLE.
MOVE PVS0209 TO A50284.

6655

R

0 12/5/11 RVU DRAWING RELEASE.

6568

R

DESCRIPTION

ECN - R

CUST SUP

DRAWN BY RVU

DATE 12/5/11

CHK'D

MAT'L:

SIGN TYPE	MATERIAL CODE
PPS	PPS - POLYESTER WITH OVERLAMINATE
PVS	GMV1 VINYL

SCALE NTS

DRAWING NO.

C10952

DWG

A
SIZE