




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:



1. DIMENSION IN [] ARE IN MILLIMETERS.

PART NUMBER	BLOCKOUT COLOR	BLOCKOUT/ PKG.	KEY/ PKG.	CTN QTY.
PSL-DCJB	RED	10	1	20
PSL-DCJB-C	RED	100	5	10
PSL-DCJB-BL	BLACK	10	1	20
PSL-DCJB-BL-C	BLACK	100	5	10
PSL-DCJB-BU	BLUE	10	1	20
PSL-DCJB-BU-C	BLUE	100	5	10
PSL-DCJB-IW	INTERNATIONAL WHITE	10	1	20
PSL-DCJB-IW-C	INTERNATIONAL WHITE	100	5	10
PSL-DCJB-YL	YELLOW	10	1	20
PSL-DCJB-YL-C	YELLOW	100	5	10
PSL-DCJB-GR	GREEN	10	1	20
PSL-DCJB-GR-C	GREEN	100	5	10
PSL-DCJB-OR	ORANGE	10	1	20
PSL-DCJB-OR-C	ORANGE	100	5	10
PSL-DCJB-IG	INTERNATIONAL GRAY	10	1	20
PSL-DCJB-IG-C	INTERNATIONAL GRAY	100	5	10



.40 REF. [10.08]
 BLOCKOUT
 MATERIAL: POLYCARBONATE
 (SEE TABLE FOR COLOR)

.20 REF. [5.18]
 KEY
 MATERIAL: BLACK NYLON

PART NUMBER		PSL-DCJB-*	
TITLE			
JACK MODULE BLOCKOUT			
CUSTOMER DRAWING			
ITEM REVISION NAME		100619CP/04	
DATASET FILE NAME		100619CP_DC_C10380/04A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		 MATERIAL: SEE DRAWING	
.x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °			
DRAWING NUMBER:		C10380	
THIRD ANGLE PROJECTION			
DRAWN BY	DATE	CHK	SCALE
RVU	9-15-05	DWY	NONE
SHT 1 OF 1		A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
5	2-28-17	BJN	JAV	AMY	UPDATED REVISED & REDRAWN PREVIOUS REVS REMOVED FOR CLARITY	C10380

D10100DA/14