


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	PACKAGE QTY.	MAX BUNDLE DIA	"LENGTH" ±.3 [ 7 ]
MLTFC2H-LP316	50	2" [ 51 ]	7.9"[ 201 ]
MLTFC2.7H-LP316	50	2.7" [ 69 ]	10.15"[ 258 ]
MLTFC4H-LP316	50	4" [ 102 ]	14.3"[ 362 ]
MLTFC6H-LP316	50	6" [ 152 ]	20.5"[ 521 ]
MLTFC8H-LP316	50	8" [ 203 ]	26.8"[ 679 ]



NOTES:

1. APPLICATION TOOLS - GS4MT, PPTMT, ST2MT, HTMT OR ST3MT
2. MINIMUM LOOP TENSILE STRENGTH - 250 LBS. (1112 NEWTONS) WHEN TESTED ON A 1.5" MANDREL.
3. BRACKETS [ ] DENOTE DIMENSIONS IN MILLIMETERS, AND ARE SHOWN FOR REFERENCE ONLY
4. TOLERANCES:  
 .XXX = ±.010 [ .25 ]    .XX = ±.02 [ .5 ]  
 .X = ±.03 [ .8 ]    ANGLES = ±2°
5. MATERIAL: 316 STAINLESS STEEL
6. COATING - POLYESTER  
 COATING THICKNESS: .002 MIN./ .005 MAX. PER SIDE

FULLY ROUNDED EDGES ALONG STRAP BODY

SECTION A - A  
SCALE 4:1

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
04A	4/13	JAMB	MIM	RGRO	UPDATE DRAWING TO NEW GLOBAL PANDUIT TITLE BLOCK WITH PANDUIT LOGO	SSECN01047
03A	2/12	MIM	RGRO	---	NOTE #3 METRIC DIMENSIONS NOTED AS BEING SHOWN FOR REFERENCE ONLY	-----
02	11/05	JMMR	EJD	---	ADDED MLTFC2.7H-LP316 TO TABLE	SS00112
01	3/05	JAMB	PAB	JJB	DRAWING REVISED TO REFLECT CURRENT COATED HEAVY SERIES PRODUCT	12501
00	11/04	JAMB	PAB	JJB	DRAWING RELEASED	12169

TITLE						
<b>METAL LOCKING TIE - COATED HEAVY SERIES</b>						
CUSTOMER DRAWING						
ITEM REVISION NAME		N41193BS/04		<b>PANDUIT</b>		
DATASET FILE NAME		N41193BS/04				
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]				MATERIAL:		
.x ± .1 [ 2.54 ]		.xxx ± .005 [ .127 ]		316 STAINLESS STEEL		
.xx ± .01 [ .25 ]		ANGLES ± 5 °		DRAWING NUMBER:		
		THIRD ANGLE PROJECTION		N41193BS_DC		
DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1		SIZE
JAMB	11/04	PAB	2:1			A