



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	MAX. BUNDLE DIA. in/mm	RECM. FASTENER	WEIGHT lb/g/100 pcs
RER1.25-S6	1.25 (31.8)	#6 SCRW. (M3)	3.4 (1529)

NOTES:

1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE

(DIMENSIONS IN PARENTHESES ARE IN METRIC.)

CAD FILENAME/LAYERS

G0023910_PB_RER1.25_02

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

ELASTIC RETAINER, RER1.25-S6

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± N/A (.XXX) ± N/A
(.XX) ± .020(.5) ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY LGG

MAT'L:

NYLON BASE &
GLASS FILLED
RUBBER MODIFIED
NYLON 6/6 ARM

SCALE FULL

DRAWING NO.

G0023910

DWG
SIZE
A

2	12/7/04	KLN		REVISED ARM MATERIAL	GB023910	2			
1	7/21/03	JAD		REVISED ARM MATERIAL	GB023910	1			
R	6/19/01	LGG		INITIAL RELEASE-REPLACED SS-6227	GB023910	R			
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	